



 FORGEON

PERDITION

INSTRUCTIONS MANUAL
MANUAL DE INSTRUCCIONES

TECHNICAL SPECIFICATIONS

Physical

Model	FORGEON Perdition
Dimension	68mm x 123mm x 43mm
Weight	90g
Cord Length	USB 2.0 / 1,8m

Technicals

Buttons	5
Feets	No-additive PTFE Feet
Sensor	Pixart PMW3389
Switch	Omron

Tracking and response

Resolution	500-16.000 DPI
Polling rate	500-1000 Hz (1ms)
Max. Acceleration	60G
Max. Speed	400IPS




PERDITION DESCRIPTION


- 1 Left Click
- 2 Right Click
- 3 Scroll wheel
- 4 Wheel button
- 5 DPI Switch
- 6 "Foward" side button
- 7 "Back" side button
- 8 Polling Rate Switch



RECOMMENDATIONS FOR USE



Connect Perdition to the PC or via on an USB port




Download the Perdition software to configure it
https://www.forgeon.es/perdition/perdition_setup.ZIP

RECOMMENDATIONS FOR USE

For optimal performance, we recommend that you maintain a smooth, clean surface and change the surface pads when you notice a loss of gliding ability.

Perdition has a cabling range of 1.8m To ensure best performance and to avoid cable pulls or strain on the cable, we recommend that the use surface and the PC be no more than 1.2m apart.



ESPECIFICACIONES TÉCNICAS

ES

Físicas

Modelo	FORGEON Perdition
Dimensiones	68mm x 123mm x 43mm
Peso	90g
Longitud del cable	USB 2.0 / 1,8m

Técnicas

Botones	5
Pies	Pies de PTFE sin aditivos
Sensor	Pixart PMW3389
Interruptores	Omron

Seguimiento y Respuesta

Resolution	500-16.000 DPI
Polling Rate	500-1000 Hz (1ms)
Aceleración máxima	60G
Velocidad máxima	400IPS




DESCRIPCIÓN DE PERDITION


- 1 Click izquierdo
- 2 Click Derecho
- 3 Rueda de desplazamiento
- 4 Botón de la rueda
- 5 Selector de sensibilidad (DPI)
- 6 Botón lateral "Adelante"
- 7 Botón lateral "Atras"
- 8 Selector de tasa de sondeo (Polling Rate)



RECOMENDACIONES DE USO



Conecte Perdicion en el PC mediante un puerto USB




Descargue el software de Perdicion para configurarlo
https://www.forgeon.es/perdition/perdition_setup.ZIP

RECOMENDACIONES DE USO

Para un funcionamiento óptimo recomendamos que mantengas una superficie lisa, limpia y que realices un cambio de almohadillas cuando notes que pierde capacidad de deslizamiento.

Perdition tiene un rango de cableado de 1.8m. Para asegurar un mejor rendimiento y evitar tirones o tensión del cable, recomendamos que la superficie de uso y el PC no esté a más de 1,2m.





 FORGEON

PERDITION